Warranty for Sanuvox

- Full unit change-out: <u>R+ model only</u>. Requires ALL parts to be returned for full unit credit to be processed. IE: Broken or missing parts, including lamps, will be deducted from the total unit value credit amount.
- 2) ALL other Sanuvox units are REPAIR ONLY.
- 3) See Sanuvox Warranty Quick Reference Guide for all other parts.
- 4) Diagnostic assistance: To determine required parts or for troubleshooting assistance please contact Sanuvox directly at 888-726-8869 or write at <u>techsupport@sanuvox.com</u>. Each troubleshooting call will be assigned a Call Number and should be included on the warranty request form.



Warranty Quick Reference

| Model / Series | Ballast | Lamp | LCD Screen | Electronics | Motor | | |
|------------------|--------------------|--------------------------------|--------------------------------|--------------------------------|--------------------------------|--|--|
| SABER16/24-GM2 | 5 Years | 1 Year | n/a | n/a | n/a | | |
| SABERPW16/24-GM2 | GM2 5 Years 1 Year | | 1 Year | n/a | n/a | | |
| SR + / SR-Max | 3 Years | 3 Years | 3 Years | 3 Years | n/a | | |
| *R + / R-Max | 3 Years | 3 Years | 3 Years | 3 Years | n/a | | |
| HRV8-GX | 3 Years | 3 Years | n/a | n/a | n/a | | |
| HRV10-GX | 3 Years | 3 Years | n/a | n/a | n/a | | |
| P900 | 3 Years | 2Y Commercial / 3Y Residential | | |
| MB500-GX | 3 Years | 2 Years | n/a | n/a | 1 Year | | |
| QUATTRO-GX | 2 Years | 2Y Commercial / 3Y Residential | n/a | n/a | n/a | | |
| S300FX-GX | 3 Years | 2Y Commercial / 3Y Residential | n/a | n/a | 2Y Commercial / 3Y Residential | | |
| S1000FX-GX | 2 Years | 2 Years | n/a | n/a | 1 Year | | |
| BIOWALL SERIES | 15 Years | 2 Years | 1 Year | 1 Year | n/a | | |
| RT SERIES | 2 Years | 2 Years | n/a | n/a | n/a | | |
| IL SERIES | 15 Years | 2 Years | n/a | 1 Year | n/a | | |

Ref 8/2018

*R+ includes 3 year full unit replacment warranty. Not valid for any other models.



Ballast Cross Reference

| | Sabei | APR | R1500 | R3500 | R17 | 700 | R40 | 000 | SI | { + | SR-Max | F | ! + | R-Max | Qua | ittro | S3 | 00 | |
|-----------------------------|--------------------|---------------------------|-----------------|-----------------|---------------------------|---------------------------|---------------------------|---------------------------|---------------------------|---------------------------|--------------------|---------------------------|---------------------------|--------------------|---------------------------|---------------------------|---------------------------|---------------------------|--|
| Generation Ballast Model | Before Feb 2011 | After Feb 2011 | | | Before April 2011 | After April 2011 | Before July 2009 | After July 2009 | Before Sept 2014 | After Sept 2014 | After July 2018 | Before Oct 2014 | After Oct 2014 | After July 2018 | Before June 2010 | After June 2010 | Before Aug 2010 | After Aug 2010 | |
| BST120/240G18 | | | Original | Original | | | | | Original | | | | | | | | | | |
| BST120/240GL | | | Replacement See | Replacement See | | | | | | | Original | Original | | | | | | | |
| B31120/2400L | | | Note 2 | Note 2 | | | | | Replacement see note 2 | Replacement see note 3 | Original | | | | | | | | |
| BST120/240GL7 | Original | | | | | | | | | | | | | | | | | | |
| BST120/240GL20 | Replacement see | | | | Original | | Original | | | | | | | | Original | | Original | | |
| B31120/240GL20 | note 3 | | | | Unginar | | Ungillar | | | | | | | | Replacement see note 3 | | Replacement see note 3 | | |
| BST120/277GL | | Original | | | | Original | | Original | | | | Original | | | | Original | | Original | |
| B31120/2//GL | | Replacement See Note 1 | | | Replacement see note 1 | Replacement see note 1 | Replacement see note 1 | Replacement see note 1 | | | | Replacement see note 3 | | | | Replacement See note 3 | | Replacement see note 3 | |
| BST120/277GLR | | | | | | | | | | | | | Original | Original | | | | | |
| BST120/2//GLK | | | | | | | | | | | | | Replacement see note 3 | C. Biller | | | | | |

| Note 1 |
|---|
| The replacement ballast must be secured in the housing with adhesive tape. Includes: adhesive tape, cable and instruction |
| Note 2 |
| An additional hole must be made during installation. Includes: instruction |
| Note 3 |
| The replacement ballast must be identical to the new Ballast. |



BST120/277GL



BST120/277GLR



BST120/240GL



BST120/240GL20

Sanuvox Lamp Date Codes

Sanuvox utilizes two lamp manufacturers for our Ultraviolet Lamps. Each manufacturer uses different date codes for production dates as follows:

Top picture: <u>F2410</u> Represents the date code (week/year): (F) Mfg code, (24) Week lamp was built, (10) Year lamp was built. This example: Top pictured lamp built 24th week of 2010.

Or

Bottom picture: <u>12054</u> Represents the date code (day/year): (12) Year Lamp was built, (054) Day lamp was built. This example: Bottom pictured lamp built 54th day of 2012.



| | | | | REFERENCE GUIDE ON SANUVOX LAMPS | | |
|--------------|------------|------------|-----------|---|----------|--------|
| PART NUMBER | FORMAT | GERMICIDAL | OXYDATION | MODELS USED | SHAPE | COLORÉ |
| LMPRGPT160T5 | LAMP 15" | Х | | SABER16/24-GM , SABER16/24-GM2, SABERSMART, SABERGN16/24110-G, SABERPW16/24-GM2 | STRAIGHT | WHITE |
| LMPRGPT120 | LAMP 12" | Х | | SABER 12 , SABER APR 12 | STRAIGHT | WHITE |
| LMPRGPT180 | LAMP 18" | Х | | SABER 18 , SABER APR 18 | STRAIGHT | WHITE |
| LMPRGXJ105 | LAMP 10.5" | Х | Х | R3500-GX , HRV8-GX | «J» | WHITE |
| LMPRGXJ65 | LAMP 6.5" | Х | Х | R1500-GX , HRV6-GX , P800-GX, P900-GX , MB500-GX , CMU18-GX, SRPLUS+, SRMAX | «J» | WHITE |
| LMPRGJ105 | LAMP 10.5" | Х | | R3500-G , HRV8-G | «J» | WHITE |
| LMPRGJ65 | LAMP 6.5" | Х | | R1500-G , HRV6-G , P800-G , P900-G , MB500-G , CMU16-G | «J» | WHITE |
| LMPRXJ105 | LAMP 10.5" | | Х | R3500-X , HRV8-X | «J» | BLUE |
| LMPHXJ160 | LAMP 16" | | Х | C2000-X , S1000FX-X | «J» | BLUE |
| LMPRGXJ160 | LAMP 16" | Х | Х | C2000G-X , S1000FX-GX | «J» | WHITE |
| LMPRGJ160 | LAMP 16" | Х | | C2000-G , S1000FX-G | «J» | WHITE |
| LMPHGXJ65 | LAMP 6.5" | Х | Х | R1700-GX | «J» | YELLOW |
| LMPHXJ65 | LAMP 6.5" | | Х | R1700-X | «J» | BLUE |
| LMPHGXJ105 | LAMP 10.5" | Х | Х | R4000-GX , S300FX-GX, RPLUS +, RMAX | «J» | YELLOW |
| LMPHXJ105 | LAMP 10.5" | | Х | R4000-X, S300FX-X | «J» | BLUE |
| LMPHGJ65 | LAMP 6.5" | Х | | R1700-G , ALL MODELS TOTALINE | «J» | PURPLE |
| LMPHGJ105 | LAMP 10.5" | Х | | R4000-G , S300FX-G , ALL MODELS TOTALINE | «J» | PURPLE |
| LMPHGXS180 | LAMP 18" | Х | Х | QUATTRO-GX | STRAIGHT | YELLOW |
| LMPHGS180 | LAMP 18" | Х | | QUATTRO-G | STRAIGHT | PURPLE |
| LMPHXS180 | LAMP 18" | | Х | QUATTRO-X | STRAIGHT | BLUE |